


MODEL L-90 DIAGRAM WITH HINGED TOP GUIDES



NOTES:

1. THE CABINET BOX SHOWN IN THE DIAGRAM IS FOR REFERENCE ONLY AND IS NOT PROVIDED WITH THE LIFT SYSTEM
2. UTILIZE PLATFORM BOX TO MOUNT THE LIFT MECHANISM AS HIGH AS POSSIBLE IN THE CABINET FOR OPTIMAL RIGIDITY
3. PLATFORM BOX HEIGHT IS DEPENDANT ON THE TV HEIGHT
4. FOR THIS LIFT MODEL, THE LENGTH OF ITS TRAVEL [EXTENSION LENGTH OR STROKE] IS 50"
5. FOR THIS LIFT MODEL, THE TOTAL WEIGHT CAPACITY IS 200 LBS
6. HEIGHT OF THIS MODEL IS ADJUSTABLE IN 1/2" INCREMENTS UP TO 8" [MINIMUM HEIGHT = 24.7"; MAXIMUM HEIGHT = 32.7"]
7. LIFT ENCLOSURE'S REAR PANEL SHOULD BE CONSTRUCTED TO WITHSTAND A LOAD OF AT LEAST 600 LBS
8. LID IS DESIGNED TO FLOAT WITH PROVIDED TAPERED PINS - LID MUST BE REMOVEABLE FOR SAFETY
9. WHEN DETERMINING TV HEIGHT, ALWAYS USE MANUFACTURER SUPPLIED "TV WITHOUT STAND" HEIGHT
10. LIFT MECHANISM IS POWDERCOATED BLACK STEEL - COLORS IN DIAGRAM ARE FOR CLARITY ONLY

IMPORTANT HINGED LID INFORMATION

1. HINGED LIDS REQUIRE THE USE OF THE "HINGED TOP GUIDE" ACCESSORY. THESE GUIDES ARE MOUNTED OT THE TOP OF THE LIFT SYSTEM AND WILL PUSH THE LID OPEN AS THE LIFT EXTENDS. WHEN THE LIFT IS LOWERED, THE LID CLOSES BY GRAVITY. PLEASE NOTE: THE LID MUST NOT OPEN BEYOND 90 DEGREES.
2. HINGES FOR THE LID ARE NOT PROVIDED BY NEXUS 21
3. FOR THE HINGED LID TO FUNCTION PROPERLY YOU MUST ALLOW AT LEAST 2" OF SPACE BETWEEN THE PIVOT POINT OF THE HINGE AND THE BACK OF THE LIFT SYSTEM. PLEASE BE AWARE SOME HINGE STYLES - SUCH AS EUROPEAN HINGES - MAY INCREASE THE OVERALL DEPTH THAT IS REQUIRED INSIDE THE CABINET. PLEASE CALL US IF YOU HAVE ANY QUESTIONS.

nexus²¹
CONCEALMENT SYSTEMS

COPYRIGHT 2016 - ALL RIGHTS RESERVED
UPDATED 05/06/16